



REV.	ECN. NO.	APPD.
A		

NOTES.
Rated Current:1.0AMP.
Contact Resistance:20mΩ Max.
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min.
Operation Temperature:-40℃ to +105℃



Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:PA9T+30%G.F UL94V-0 BK

Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP315-12XX S2



X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.			
.X ± 0.20	.X° ± 2°	MAT'L					
.XX ± 0.10	.XX° ± 1°	FINISH	PART NO.(INTENDED USE)	TITLE: PH1.27 DUAL ROW 180° H=1.5			
.XXX ± 0.05	.XXX° ± 0.5°		APPD: SUNNY	DWG NO.: MTP315-12XXS2			
PIN HEADER CONNNECTOR		Q'TY	CHKD: LISA		SCALE	SHEET	REV.
			DR: ZOE 2006-11-28		1/1	1/1	A