




A B C D E F



N=PIN数



Material 材料  
 Insulator 塑胶: PBT PA9T (UL 94V-0)  
 Contact 端子: Brass 黄铜  
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金  
 Electrical Characteristics 电气特性  
 Current rating 额定电流: 2.5Amps  
 Dielectric Withstanding Voltage 耐压:  
     AC 500V for 1 Minute.  
 Insulator Resistance 绝缘电阻: 1000MΩ Min.  
 Contact Resistance 接触电阻: 20mΩ Max.  
 Operating Temperature 工作温度: -40°C ~ +105°C  
 Max. Processing Temp 瞬时温度:  
     240° C for 30-60 seconds  
     (260° C for 10 seconds)



P.C.B LAYOUT

未注尺寸公差			PIN2*40 2.54 S		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD					
尺寸	公差								版本编号	20171018 A/O
X.	±0.3	±5°	图纸编号	ZR20171018-257	TEL:86-21-34975176/51571121					
X.X	±0.2	±3°	制图	周元金 201171018	物料编号		1:1	mm	图幅	A4
X.XX	±0.15		审核	张海娜 201171018	第三视角					
			核准	章妹 201171018						

A B C D E F