



PCB LAYOUT



Material
 Insulator: Glass filled PBT, (UL 94V-0)
 Contact : Brass

Electrical Characteristics
 Current rating: 2AMP
 Dielectric Withstanding Voltage: AC 500V for 1 Minute.
 Insulator Resistance: 1000MΩ Min. AT DC 500V.
 Contact Resistance: 20mΩ Max.
 Operating Temperature: -45°C ~ +105°C

PIN 尺寸	A±0.15	B±0.2	C±0.2	D±0.1
DR-9F	16.50	25.00	30.80	12.50
DR-15F	24.80	33.30	39.20	12.50
DR-25F	38.55	47.10	53.10	12.50
DR-37F	54.90	63.50	69.44	12.50

		D-SUB-DR*F		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD			
				上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Electronic Equipment import and export Co.,LTD			
X.	±0.3	±5°		20171018 A/0		TEL:86-21-34975176/51571121	
X.X	±0.2	±3°		20171018		20171018-DR-103	
X.XX	±0.15			20171018		物料编号	
				20171018		: 1 1	
				20171018		mm 图幅 A4	

