












RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



SCHMATIC



P. C. B LAYOUT

- ELECTRICAL CHARACTERISTICS
1. RATING:DC 30V 0.1A
 2. CONTACT RESISTANCE: 100MΩ MAX
 3. INSULATION RESISTANCE:100MΩ MIN
 4. DIELECTRIC STRENGTH:AC 250V (50~60HZ)/60S
- MECHANICAL CHARACTERISTICS
1. PRACTICAL TEMPERATURE RANG:-40°C~+85°C
 2. OPERATING FORCE:180±50GF
 3. MECHANICAL LIFE:20000 CYCLES

7	LOCK PIN	SUS WIRE	1	NATURAL
6	CASE	BRASS	6	AG PLATED
5	SPRING	PPA	1	GRAY
4	CONTACT	SUS WIRE	1	NATURAL
3	KNOB	BRONZE	2	AG PLATED
2	COVER	PPA	1	WHITE
1	cover	PPA	1	BLACK
NO.	PART NAME	MATERIAL	QTY	FINISHING

X. ±0.50	X.° ± 5°	UNITS mm
.X ±0.30	.X° ± 2°	
.XX ±0.20	.XX° ± 1°	MAT'L
.XXX ± 0.1	.XXX ± 0.5°	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH
		Operation Force 180GF

yiYUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO. YTS58L180AWS	TITLE: 按钮类5.8*5.8 自锁键2*2.5按钮类
APPD: ROGER	DWG NO.: YTS58L180AWS
CHKD: RDC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	