



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—/#—						
			F2	REVISED PER ECR-20-100273	12AUG20	WH	DZ



—/#—	PRE TIN BRASS 無めっき黄銅	1123721-2
1318912-1	PRE TIN PHOS BRO 無めっき黄銅リン青銅	1123721-1
バラ端子型番 (LOOSE PIECE CONT P/N)	材料 (MATERIAL)	型番 (Part Number)

WIRE RANGE 組合電線断面積	0.3~0.89mm ² (AWG#22~18)	INSULATION DIA 被覆外径	φ1.7~3.0mm
-----------------------	-------------------------------------	------------------------	------------

DIMENSIONS: 単位: 寸 mm	DWN	24 JUN '98	N.YAMASAKI	MATERIAL 表参照 (SEE LABEL)	FINISH 仕上 ——#——			
	CHK	24 JUN '98	M.SHINDO	 TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 5 ± : ±0.3 5 > : ±0.4	APVD	24 JUN '98	M.SHINDO					
	PRODUCT SPEC 製品規格		108-5609	NAME 名称 ECONOMY POWER(EP) CONN. REC CONT エコノミパワー(EP) コネクタ リセコンタクト				
	APPLICATION SPEC 取付適用規格		114-5253	SIZE A4	CAGE CODE 00779	DRAWING NO 番号 C=1123721	RESTRICTED TO	
	WEIGHT		——#——	CUSTOMER DRAWING				
				SCALE 尺度	——#——	SHEET 1	OF 1	REV F2

参考図面