



PCB LAYOUT



Material  
Insulator: Glass filled PBT, (UL 94V-0)  
Contact : Brass

Electrical Characteristics  
Current rating: 2AMP  
Dielectric Withstanding Voltage: AC 500V for 1 Minute.  
Insulator Resistance: 1000MΩ Min. AT DC 500V.  
Contact Resistance: 20mΩ Max.  
Operating Temperature: -45°C ~ +105°C

PIN	尺寸	A±0.15	B±0.2	C±0.2	D±0.1
DR-9M		17.90	25.00	30.80	12.50
DR-15M		26.50	33.30	39.20	12.50
DR-25M		40.00	47.10	53.05	12.50
DR-37M		56.50	63.50	69.44	12.50

			D-SUB-DR-*M		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD		
X.	±0.3	±5°			上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD		
X.X	±0.2	±3°			TEL:86-21-34975176/51571121		
X.XX	±0.15				201171018		
			物料编号		201171018		
					1:1 mm 图幅 A4		
					: 1 1		