







2 CODING B.C
2322347-2 AS SHOWN




1 CODING A.D
2322347-1 AS SHOWN



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		NEW PRODUCT RELEASED	31AUG2017	T.D	I.Y
B		ECR-19-004905	13JUN2019	J.L	I.Y

RETAINER CLOSED PICTURE




6 OPEN GUIDE:
TO OPEN THE LOCKED RETAINER, USE A Ø 1X0.18MM
SCREWDRIVER AND PUSH IT IN THE SHOWN OPENING.

NOTES

- 1 MATING PART EXECUTION TO INTERFACE 114-101068
- 2 SUITABLE CONTACT
MQS: 1355717, 928999, 963715
MCP2.8K: 1241386, 1241388, 1241390
- 3 SUITABLE MATING HOUSING 2311788/2321709
- 4 MATERIAL REMOVAL OPTIONAL IN EXECUTION AND POSITION ACC.
TO MANUFACTURE POSSIBLE
- 5 PACKAGE: LOOSE PIECE IN CARTON BOX

6 CONDITION ON DELIVERY:
SECONDARY LOCK DEVICE SHOULD BE IN PRELOCK POSITION
--IF IN ENDLOCK POSITION AFTER TRANSPORTATION,
PLEASE REOPEN IT IN ACCORDANCE THE OPENING GUIDE

2322347-4	B	B.D	PBT-GF10	BLUE	5012	1.976	2.71	4
2322347-3	B	A.C	PBT-GF10	GREEN	6018	1.976	2.71	3
2322347-2	B	B.C	PBT-GF10	BROWN	1011	1.976	2.71	2
2322347-1	B	A.D	PBT-GF10	BLACK	9011	1.976	2.71	1
TE-PART NO	REV.	COD.	MATERIAL	COLOUR	RAL	VOLUME [cm 3]	WEIGHT [g]	POS.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T.DONG 16AUG2017	 TE Connectivity				
DIMENSIONS: mm			CHK E.JIANG 31AUG2017					
			APVD I.YIN 31AUG2017	NAME HYBRID MQS 8POS./MCP2.8K 4POS.. REC.. HSG.				
			PRODUCT SPEC 108-101599					
TOLERANCES UNLESS OTHERWISE SPECIFIED			APPLICATION SPEC	SIZE CAGE CODE DRAWING NO A 1 00779 C=2322347				
0 PLC ±			WEIGHT -					
1 PLC ±			CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV B				
2 PLC ±								
3 PLC ±								
4 BCC ±								
FINISH								
SEE TABLE								