

REV.	SPECIFICATION	ECN NO.	APPD.
R1			






Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.
 Contacts: Copper Alloy.

Electrical Characteristics:

Current Rating: 2 A.
 Dielectric Withstanding Voltage: AC 1000V for 1minute.
 Insulator Resistance: 1000MΩ min. at DC 500V.
 Contact Resistance: 20mΩ max. at DC 100m A.
 Operating Temperature: -55°C ~ +125°C .

* **RoHS Compliant**



P.C. Board Layout

9001- 3 4 xx 1 C xx A
 Series
 3: 2.54mm
 4: Female
 Position
 1: Dip Length
 A: Tray Package
 00: G/F
 10: 10u
 12: 12u
 30: 30u
 C: Dip Tin Contact Gold
 G: Gold

Pitch	Position	Rows with Contacts	Contact Arrange	P/N
2.54mm	64	a b	4321	9001-34641CxxA
	32	a -	4321	9001-34321CxxA

Tolerances	Drawn No.	9001D34001	
x = ±0.5	Projection		
.x = ±0.25	Unit	mm	Scale 1:1
.xx = ±0.15	Drawn By	Rikey 02/02'10	

Title: 9001 Series
 DIN41612 Q Type Female

WINGTAT [®]			
深圳市格林柏电子技术开发有限公司			
P/N: 9001-34xx1CxxA			
SHEET	1/1	Ver.No.	R1