








修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2012-01-16


Specifications:

Poles: 20 to 50
 Contact resistance: $\leq 20\text{m}\Omega$
 Insulation resistance: $\geq 100\text{M}\Omega$
 Rated voltage: 50V AC DC
 Rated current: 0.8A AC DC
 Withstand Voltage: 250V AC/minute
 Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 Housing: PA9T UL94V-0, Natural
 Contacts: Phosphor Bronze/ Gold-plated
 Solder tabs: Brass/MATTE Sn-plated
 Cap: PA9T UL94V-0, Natural



PCB LAYOUT(Tolerance: ± 0.05)

PIN.	DIM A	DIM B	DIM C	DIM D
2x10P	9.00	12.30	10.45	11.25
2x15P	14.00	17.30	15.45	16.25
2x20P	19.00	22.30	20.45	21.25
2x25P	24.00	27.30	25.45	26.25

 深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD TEL : 0755-27111225 FAX : 0755-29940187				TITLE: 产品名称: MX1.0双排针座			
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表						PART NO: 产品编号: HDGC1008WV-S-2xXP	
X.X	± 0.30	X.X°	$\pm 3^{\circ}$	APPD: 核准: 谢亮	DATE		
X.XX	± 0.30	X.XX°	$\pm 2^{\circ}$	CHECK: 校对: 王建业	SCALE	UNIT	CODE NUMBER
X.XXX	± 0.10	X.XXX°	$\pm 1^{\circ}$	DRAW: 绘图: 黄艳兰	2012-01-16	5:1	mm A018