



辅助开关，1 NO +1 NC，20-150ms 超前，带镀金触点，用于四孔前面固定，用于底部固定和 注塑外壳，附件用于主开关和 急停开关 3LD2 用于 160A-250A 并用于 主开关和急停开关 3LD5 UL 用于 100A-150A

版本	
产品品牌名称	SETRON
产品名称	辅助开关（超前）
产品的规格	附件，用于主开关和紧急停止按钮开关3LD2，维护开关和维修开关 3LD2，带EMC屏蔽板
工作电流	
• AC-15 时 / 48 V 时 / 测定值	10 A
• AC-15 时 / 110 V时 / 测定值	6 A
• AC-15 时 / 230 V时 / 测定值	3 A
• AC-15 时 / 400 V 时 / 测定值	1.7 A
• AC-15 时 / 500 V 时 / 测定值	1.5 A
• DC-13 时 / 110 V时 / 测定值	0.25 A
• DC-13 时 / 48 V 时 / 测定值	0.5 A
• DC-13 时 / 24 V 时 / 测定值	1 A
超前时间 / 基于主触点	20 ms
可连接的导线截面类型 / 用于辅助触点	
• 单芯线的	1x (0.75 ...2.5 mm²)
• 细芯线的 / 带有电缆末端加工	1x (0.75 ...2.5 mm²)
• 多芯线	1x (0.75 ...2.5 mm²)
General Product Approval	
Declaration of Conformity	



[Confirmation](#)



Declaration of Conformity	Test Certificates	other
---------------------------	-------------------	-------



[Special Test Certificate](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

Information- and Downloadcenter (产品目录, 产品介绍册, ...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (网上订购系统)

<https://mall.industry.siemens.com/mall/zh/zh/Catalog/product?mlfb=3LD9240-5DF>

Service&Support (用户手册, 操作说明书, 认证证书, 特性曲线, 常见问题,...)

<https://support.industry.siemens.com/cs/ww/zh/ps/3LD9240-5DF>

图片数据库 (产品照片, 2D比例图, 3D模型, 设备电路图, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD9240-5DF

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



