







N=PIN数



P.C.B LAYOUT

Material 材料  
 Insulator 塑胶: PA46 PA6T (UL 94V-0)  
 Contact 端子: Brass 黄铜  
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金  
 Electrical Characteristics 电气特性  
 Current rating 额定电流: 1.0Amps  
 Dielectric Withstanding Voltage 耐压:  
     AC 500V for 1 Minute.  
 Insulator Resistance 绝缘电阻: 1000MΩ Min.  
 Contact Resistance 接触电阻: 20mΩ Max.  
 Operating Temperature 工作温度: -40°C ~ +105°C  
 Max. Processing Temp 瞬时温度:  
     240° C for 30-60 seconds  
     (260° C for 10 seconds)

| 未注尺寸公差 |       |           | PZ2.0-1*N |                | 上海洲日电子有限公司<br>Shanghai Zhouri Electronics CO.,LTD<br>上海康司玛电子设备进出口有限公司<br>Shanghai KangSiMa Eletronic Equipment<br>import and export Co.,LTD<br>TEL:86-21-34975176/51571121 |  |  |  |
|--------|-------|-----------|-----------|----------------|--|--|--|--|
| 尺寸     | 公差    |           |           |                |  |  |  |  |
| X.     | ±0.3  | ±5°       | 版本编号      | 20171018 A/O   | 1:1 mm 图幅 A4   |  |  |  |
| X.X    | ±0.2  | ±3°       | 图纸编号      | ZR20171018-241 |  |  |  |  |
| X.XX   | ±0.15 |           | 物料编号      |                | : 1 1  |  |  |  |
| 制图     | 周元金   | 201171018 | 第三视角      |                |  |  |  |  |
| 审核     | 张海娜   | 201171018 |           |                |  |  |  |  |
| 核准     | 章妹    | 201171018 |           |                |  |  |  |  |