

F

E

D

C

B

A

F

E




D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2013.05.04	李芳忠



Specifications
Current Rating:3Amp
Insulation Resistance:1000MΩMin.
Dielectric Withstanding Voltage:600VAC
Contact Resistance:20mΩMax.
Operating Temperature:-40°C to +105°C
Materials
Contact Material:Phosphor Bronze
Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T(Halogen Free) or the equivalent material
All materials must meet Greenconn requirement for environment protection.


Ordering Information

G PHA201 - XX XX A 001 R 1 A X

No. of Pins per Row 01~40 Standard Plating 02=Gold Flash Selective Plating 01=Tin 05=Gold Flash/Tin

Color 1=Black Standard Packing A=Box Selective Packing C=Tube

Recommended P.C.Board Layout
(Tolerance:±0.05)



格稜股份有限公司 Greenconn Corporation			GENERAL TOLERANCE X.*±5.0° X.±0.30 .X*±3.0° .X±0.25 .XX*±2.0° .XX±0.15 .XXX*±1.0° .XXX±0.10		DESIGN: 李芳忠	DATE: 2013.05.04	DWG. NO. GPHA201-CA1RA	TITLE. 2.54 PIN HEADER DUAL ROWS DIP TYPE CONNECTOR
					CHECKED: 劉北平	DATE: 2013.05.04		
REV. 01	UNIT. mm	SCALE. 3:1	PAGE. 1/1		AUDITED:	DATE:	PART NO. GPHA201-XXXX A001R1AX	
					APPROVED:	DATE:		