




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
04	△	變更料號	2009.02.25	趙章池
05	△	依上級要求變更圖號	2012.05.21	李芳忠




Specifications
 Current Rating: 2Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Phosphor Bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 Nylon 6T or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Ordering Information

△ C SFA101 - XX XX A 001 B 1 A X

No. of Pins per Row: 02~40
 Standard Plating: 02=Gold Flash
 Selective Plating: 01=Tin, 05=Gold Flash/Tin
 Color: 1=Black
 Standard Packing: A=Box
 Selective Packing: C=Tube, E=Cap+Tube, F=Cap+Tape&Reel

Recommended P.C.Board Layout



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2012.05.21
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2012.05.21
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2012.05.21
.XX*±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2012.05.21
.XXX*±1.0°	.XXX±0.10		

DWG. NO.	△△ CSFA101-CA1BA
PART NO.	△ CSFA101-XXXX A001B1AX

TITLE:
 2.00 FEMALE HEADER
 SINGLE ROW DIP TYPE
 CONNECTOR

REV. 05	UNIT. mm	SCALE. 5:1	PAGE. 1/1	
---------	----------	------------	-----------	--