


REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2012.01.30	李芳忠




Specifications
 Current Rating:2Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T(無鹵) or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Ordering Information

G PFA104 - XX XX A 040 R 1 B X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing A=Box
 Selective Packing C=Tube

Recommended P.C.Board Layout
 (Tolerance:±0.05)



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGN: 李芳忠	DATE: 2012.01.30	DWG. NO.	TITLE: 2.00 PIN HEADER SINGLE ROW DIP TYPE CONNECTOR
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2012.01.30	GPFA104-CA40RB	
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2012.01.30	PART NO.	
.XX*±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2012.01.30	GPFA104-XXXX A040R1BX	
.XXX*±1.0°	.XXX±0.10				

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1