



PCB LAYOUT

Specifications:  
 规格:  
 Voltage rating: 250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating: 1A AC/DC  
 额定电流: 1A AC/DC  
 Withstanding voltage: 300V AC/minute  
 耐受电压: 300V AC/分钟  
 Temperature range: -40°C-+105°C  
 温度范围: -40°C-+105°C  
 Insulation resistance: ≥500MΩ  
 绝缘电阻: ≥500MΩ  
 Contact resistance: ≤20mΩ  
 接触电阻: ≤20mΩ  
 Material: PA6T UL94V-0  
 材质: PA6T UL94V-0  
 Plating Category: 1U"Gold  
 镀层: 1U"Gold  
 Wave soldering temperature: 255±5°C, 10S  
 波峰焊温度: 255±5°C, 10S

X1322 W R - 2xXX K - C40 D30 - E14 F06  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No.
2. Category: W-Water
3. Welding Board Angle: R-Straight 90°
4. Row No -Pin No: 2xXX-2x02P-2x40P
5. Plastic height: K=1.5mm
6. Pin length: C=4.0mm
7. Pin length: D=3.0mm
8. Pin length: E=1.45mm
9. Pin length F=0.6mm

X1322WR-2xXXK-C40D30-E14F06	PA6T	Brass	1U"Gold	X1321F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN	VIEW:	PART NO.: X1322WR-2xXXK-C40D30-E14F06
CHKD	UNIT: mm/in	DWG NO.: X-X1322WR-2xXXK-C40D30-E14F06
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

Δ姓	日期
Δ效	日期
MARK	DESCRIPTION
文件	工程章

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn