



Specifications:  
 规格:  
 Voltage rating: 250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating: 1A AC/DC  
 额定电流: 1A AC/DC  
 Withstanding voltage: 300V AC/minute  
 耐受电压: 300V AC/分钟  
 Temperature range: -40°C +105°C  
 温度范围: -40°C +105°C  
 Insulation resistance: ≥500MΩ  
 绝缘电阻: ≥500MΩ  
 Contact resistance: ≤20mΩ  
 接触电阻: ≤20mΩ  
 Material: PA6T UL94V-0  
 材质: PA6T UL94V-0  
 Plating Category: 1U" Gold  
 镀层: 1U" Gold  
 Wave soldering temperature: 255±5°C, 10S  
 波峰焊温度: 255±5°C, 10S

X1322 W V - 2xXX H - C40 D30 - E80  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1. Series No.
2. Category: W-Water
3. Welding Board Angle: V-Stright 180°
4. Row No -Pin No: 2xXX-2x02P-2x50P
5. Plastic height: H=2.5mm
6. Pin length: C=4.0mm
7. Pin length: D=3.0mm
8. Pin length: E=8.0mm

PCB LAYOUT

X1322WV-2xXXH-C40D30-E80	PA6T	Brass	1U"Gold	X1321F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
Δ*	日期				L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN	VIEW:	PART NO.: X1322WV-2xXXH-C40D30-E80
CHKD	UNIT: mm/in	DWG NO.: X-X1322WV-2xXXH-C40D30-E80
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED

文件工程章