



P.C.B LAYOUT

Specifications:
 规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating:2A AC/DC
 额定电流: 2A AC/DC
Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
Temperature range:-40°C-+105°C
 温度范围: -40°C-+105°C
Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
Material:PA6T UL94V-0
 材质: PA6T UL94V-0
Plating Category:1U"Gold
 镀层: 1U"Gold
Wave soldering temperature:255±5°C, 10S
 波峰焊温度: 255±5°C, 10S

X4621 W R - 2xXX I - C40 D28
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category:W-Wafer
3. Welding Board Angle:R-Stright 90°
4. Row No.Pin No:2xXX-2x01~2x40P
5. Plastic Height:l=2.0mm
6. Pin Length:C=4.0mm
7. Pin Length:D=2.8mm

X4621WR-2xXXI-C40D28	PA6T	Brass	X4621F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ生					ANGLAR ±5°
Δ数					L ≤ 4 ±0.2
Δ*					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN	VIEW:	PART NO.: X4621WR-2xXXI-C40D28
CHKD	UNIT: mm/in	DWG NO.: X-X4621WR-2xXXI-C40D28
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED