



P.C.B LAYOUT

Specifications:
 规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-40°C-+105°C
 温度范围: -40°C-+105°C
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ
 Material:PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category:1U"Gold
 镀层: 1U"Gold
 Wave soldering temperature:260±5°C, 10S
 波峰焊温度: 260±5°C, 10S

X4622 W V S - 2xXX I - C40 D64 - E60
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Straight 180°
- 4.Welding Way: S-SMT
- 5.Row No.Pin No:2xXX-2x02~2x40P
- 6.Plastic Height:l=2.0mm
- 7.Pin Length:C=4.0mm
- 8.Pin Pitch:D=6.4mm
- 9.Pin Length:E=6.0mm

X4622WVS-2xXXI-C40D64-E60	PA6T	Brass	X4621F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.0mm BTB Connector
DWN	VIEW:	PART NO.: X4622WVS-2xXXI-C40D64-E60
CHKD	UNIT: mm/in	DWG NO.: X-X4622WVS-2xXXI-C40D64-E60
APPD	SIZE: A4	



XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

Δ姓	日期
Δ数	
ΔX	

MARK DESCRIPTION DATE REVISED APPROVED

文件工程章 REVISIONS UNSPECIFIED TOLERANCES