





版次	日期	变更内容	变更单号	变更者
1.0	13.8.5	原始版本		

20	19.0	22.0	21.3
19	18.0	21.0	20.3
18	17.0	20.0	19.3
17	16.0	19.0	18.3
16	15.0	18.0	17.3
15	14.0	17.0	16.3
14	13.0	16.0	15.3
13	12.0	15.0	14.3
12	11.0	14.0	13.3
11	10.0	13.0	12.3
10	9.0	12.0	11.3
9	8.0	11.0	10.3
8	7.0	10.0	9.3
7	6.0	9.0	8.3
6	5.0	8.0	7.3
5	4.0	7.0	6.3
4	3.0	6.0	5.3
3	2.0	5.0	4.3
2	1.0	4.0	3.3
Poles	A	B	C



P.C.B LAYOUT REF

技术参数

额定电压: 50V AC DC  
 额定电流: 1A; AC, DC  
 耐压值: 200V. min/AC  
 绝缘电阻: 100MΩ, Min  
 接触电阻: 20mΩ Max  
 耐压 Withstanding Voltang 500V

工作温度: -25°C ~ +85°C  
 间距: 1.0mm

材料  
 外壳: LCP米色  
 插针: 磷铜

1. 0T-立贴		图号	
绘制		比例	
审查		单位	mm
核准		页次	of
供应商			