







面板安装开孔图  
Panel cut out



技术参数:

插芯:

- 插针数: 16+PE
- 额定电流: 16A
- 额定电压: 250V
- 额定脉冲电压: 4kV
- 污染等级: 3
- 依据UL/CSA的额定电压: 600V
- 绝缘阻抗:  $\geq 10^{10}\Omega$
- 材料: 聚碳酸酯
- 颜色: RAL 7032 (浅灰色)
- 温度范围:  $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
- 依据UL 94的阻燃等级: V0
- 可插拔次数:  $\geq 500$
- 插针:
- 接线方式: 螺钉连接
- 材料: 铜合金
- 表面处理: 镀银
- 接触电阻:  $\leq 1\text{m}\Omega$
- 线径范围:  $0.75-2.5\text{mm}^2(18-14\text{ AWG})$
- 拧紧/检测力矩:  $0.5\text{N} \cdot \text{m}$

Technical specification:

Inserts:

- No. of contact: 16+PE
- Rated current: 16A
- Rated voltage: 250V
- Rated impulse voltage: 4kV
- Pollution degree: 3
- Rated voltage acc.to UL/CSA: 600V
- Insulation resistance:  $\geq 10^{10}\Omega$
- Material: polycarbonate
- Colour: RAL 7032(light grey)
- Temperature range:  $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
- Flammability acc.to UL 94: V0
- Mating cycles:  $\geq 500$

Contacts:

- Terminal: screw terminal
- Material: copper alloy
- Surface: hard-silver plated
- Contact resistance:  $\leq 1\text{m}\Omega$
- Wire gauge:  $0.75-2.5\text{mm}^2(18-14\text{ AWG})$
- Tightening/Test torque:  $0.5\text{N} \cdot \text{m}$

|               |              |                  |                |          |                 |                                                                                       |                                                                                       |                                               |            |                   |                   |                                                                                                                                   |  |
|---------------|--------------|------------------|----------------|----------|-----------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------------------------------------|------------|-------------------|-------------------|-----------------------------------------------------------------------------------------------------------------------------------|--|
|               |              |                  |                |          |                 | 表面处理<br>Finish                                                                        | —                                                                                     |                                               |            |                   | 图号<br>Drawing No. | —                                                                                                                                 |  |
|               |              |                  |                |          |                 | 材料<br>Material                                                                        | —                                                                                     |                                               |            |                   | 产品代号<br>Part Code | HA-016-F/B                                                                                                                        |  |
| 标记<br>Mark    | 处数<br>Number | 变更描述/Description |                |          | 签名<br>Signature | 日期<br>Date                                                                            |                                                                                       |                                               |            |                   | 产品料号<br>Part No.  | 1210160210505                                                                                                                     |  |
|               | 姓名/Name      | 日期/Date          |                | 姓名/Name  | 日期/Date         | 比例<br>Scale                                                                           | 版本<br>REV.                                                                            | 重量<br>Weight                                  | 数量<br>Qty. | 产品名称<br>Part Name | —                 |                                                                                                                                   |  |
| 绘图<br>Drawn   | ZL CHEN      | 14.12.2018       | 标准化<br>Stand.  | —        | —               | 1:1                                                                                   | V1.0                                                                                  | 62.8g                                         | —          |                   |                   |                                                                                                                                   |  |
| 审核<br>Checked | P RAO        | 14.12.2018       |                |          |                 |                                                                                       |                                                                                       |                                               |            |                   |                   |                                                                                                                                   |  |
| 工艺<br>Process | —            | —                | 批准<br>Approved | HQ ZHANG | 14.12.2018      |  |  | All Dimensions in mm<br>Original Size DIN A 4 |            |                   |                   |  厦门唯恩电气有限公司<br>XIAMEN WAIN ELECTRICAL CO.LTD |  |