








面板安装开孔图
Panel cut out



技术参数:

插芯:

- 插针数: 32/55
- 额定电流: 4A/10A
- 额定电压: 50/250V
- 额定脉冲电压: 0.8kV/4kV
- 污染等级: 2
- 依据UL/CSA的额定电压: 600V
- 绝缘阻抗: $\geq 10^{10}\Omega$
- 材料: 聚碳酸酯
- 颜色: RAL 7032 (浅灰色)
- 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
- 依据UL 94的阻燃等级: V0
- 可插拔次数: ≥ 500

插针:

- 接线方式: 冷压连接
- 材料: 铜合金
- 表面处理:
 - 镀银
 - 镀金
- 接触电阻: $\leq 3\text{m}\Omega$
- 线径范围: $0.09-0.52\text{mm}^2(28-20\text{AWG})/$
 $0.14-2.5\text{mm}^2(26-14\text{ AWG})$
- 剥线长度: 5/8mm
- 工具:
 - 冷压钳:
 - TL03(0.09-0.82mm²)
 - TL02G(0.14-4mm²)
 - 退针器: TL08/TL00

Technical specification:

Inserts:

- No. of contact: 32/55
- Rated current: 4A/10A
- Rated voltage: 50/250V
- Rated impulse voltage: 0.8kV/4kV
- Pollution degree: 2
- Rated voltage acc.to UL/CSA: 600V
- Insulation resistance: $\geq 10^{10}\Omega$
- Material: polycarbonate
- Colour: RAL 7032(light grey)
- Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
- Flammability acc.to UL 94: V0
- Mating cycles: ≥ 500

Contacts:

- Terminal: crimp terminal
- Material: copper alloy
- Surface:
 - Hard-silver plated
 - Hard-gold plated
- Contact resistance: $\leq 3\text{m}\Omega$
- Wire gauge: $0.09-0.52\text{mm}^2(28-20\text{AWG})/$
 $0.14-2.5\text{mm}^2(26-14\text{ AWG})$
- Stripping length: 5/8mm
- Tools:
 - Crimp contact tool:
 - TL03(0.09-0.82mm²)
 - TL02G(0.14-4mm²)
 - Contact removal tool: TL08/TL00

				表面处理	—			图号	—	
				材料	—			Drawing No.		
标记	处数	变更描述/Description		签名	日期				产品代号	HK-032/55-FC
Mark	Number			Signature	Date				Part Code	
		姓名/Name	日期/Date	姓名/Name	日期/Date	比例	版本	重量	数量	产品料号
						Scale	REV.	Weight	Qty.	Part No.
绘图	LJ ZOU	08.10.2018	标准化	—	—	1:1	V1.1	47.5g	—	产品名称
审核	HZ LAN	08.10.2018								Part Name
工艺	—	—	批准	HQ ZHANG	08.10.2018					
Process			Approved							
						⌀	≡	All Dimensions in mm Original Size DIN A 4		
									WAIN 厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.,LTD	