






- 技术参数:

插芯:

- 插针数: 8+PE
 - 额定电流: 16A
 - 额定电压: 500V
 - 额定脉冲电压: 6kV
 - 污染等级: 3
 - 安装金属外壳时: 16A 230/400V 4kV 3
 - 依据UL/CSA的额定电压: 600V
 - 绝缘阻抗: >10¹⁰Ω
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: -40℃ - +125℃
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500
- Technical specification:

Insters:

- No. of contact: 8+PE
 - Rated current: 16A
 - Rated voltage: 500V
 - Rated impulse voltage: 6kV
 - Pollution degree: 3
 - Mounted metal hood: 16A 230/400V 4kV 3
 - Rated voltage acc.to UL/CSA: 600V
 - Insulation resistance: >10¹⁰Ω
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: -40℃ - +125℃
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500
- 插针:

- 接线方式: 冷压连接
 - 材料: 铜合金
 - 表面处理:
 - 镀银
 - 镀金
 - 接触电阻: <1mΩ
 - 线径范围:
 - 冷压连接: 0.14-4mm²(26-12 AWG)
 - 部分装备情况下可达到4mm²

外壳:

- 材料:
 - 塑料外壳: 热塑性塑料
 - 金属外壳: 金属
 - 联锁元件:
 - 塑料外壳: 聚酰胺 (尼龙)
 - 金属外壳: 不锈钢
 - 外壳密封: 丁腈橡胶
 - 温度范围: -40℃ - +125℃
 - 依据UL 94的阻燃等级:
 - 塑料外壳: V0
 - 防护等级: IP65 (联锁状态, IEC 60529)
 - 附件:
 - 保险延迟针:
 - CESM-1.0R/CESM-1.5R/CESM-2.5R
 - 冷压钳:
 - TL02G(0.5-4mm²)
 - TL02(0.14-0.37mm²)
 - 退针器: TL01
 - 编码元件: CODE-E

Contacts:

- Terminal: crimp terminal
 - Material: copper alloy
 - Surface:
 - Hard-silver plated
 - Hard-gold plated
 - Contact resistance: <1mΩ
 - Wire gauge:
 - Crimp terminal: 0.14-4mm²(26-12 AWG)
 - partly loaded up to 4mm² is possible

Hoods/Housings:

- Material:
 - Plastic hoods/housings: thermoplastic
 - Metal hoods/housings: metal
 - Locking element:
 - Plastic hoods/housings: polyamide
 - Metal hoods/housings: stainless steel
 - Hoods/Housings seal: NBR
 - Temperature range: -40℃ - +125℃
 - Flammability acc.to UL 94: V0
 - Degree of protection: IP65 (acc.to IEC 60529 for coupled connector)
 - Accessories:
 - Relay contacts:
 - CESM-1.0R/CESM-1.5R/CESM-2.5R
 - Crimping tool:
 - TL02G(0.5-4mm²)
 - TL02(0.14-0.37mm²)
 - Contact removal tool: TL01
 - Coding element: CODE-E

						表面处理 Finish	—			图号 Drawing No.	—
						材料 Material	—			产品代号 Part Code	HQ-008/0-FC
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date				产品料号 Part No.	1300080200001
	姓名/Name	日期/Date		姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name	—
绘图 Drawn	BQ LUO	18.10.2010	标准化 Stand.	—	—	1:1	V1.0	14g	—		
审核 Checked	P RAO	18.10.2010									
工艺 Process	—	—	批准 Approved	YY LIN	18.10.2010			All Dimensions in mm Original Size DIN A 4			厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD