




日期/Date

审核
Filing Clerk

技术参数:

- 插站:
 - 插针数: 4+PE
 - 额定电流: 10A
 - 相对地额定电压: 230V
 - 相间额定电压: 400V
 - 额定脉冲电压: 4kV
 - 污染等级: 3
 - 依据UL/CSA的额定电压: 600V
 - 绝缘电阻: $>10^{10}\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: >500
- 插针:
 - 接线方式: 薄片连接
 - 材料: 铜合金
 - 表面处理: 镀银
 - 接触电阻: $<1\text{m}\Omega$
 - 线径范围: $0.14-2.5\text{mm}^2/26-14$ AWG
 (带管形接线端子线径范围: $0.14-1.5\text{mm}^2/\text{AWG16}$)

Technical specification:

- Inserts:
 - No. of contact: 4+PE
 - Rated current: 10A
 - Rated voltage-ground: 230V
 - Rated voltage-conductor: 400V
 - Rated impulse voltage: 4kV
 - Pollution degree: 3
 - Rated voltage acc.to UL/CSA: 600V
 - Insulation resistance: $>10^{10}\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: >500
- Contacts:
 - Terminal: spring terminal
 - Material: copper alloy
 - Surface: hard-silver plated
 - Contact resistance: $<1\text{m}\Omega$
 - Wire gauge: $0.14-2.5\text{mm}^2/26-14$ AWG
 (For wires with crimped ferrule, wire gauge: $0.14-1.5\text{mm}^2/\text{AWG16}$)

						表面处理 Finish		-		图号 Drawing No.		-		
						材料 Material		-		产品代号 Part Code		HA-004-MS		
标记 Mark	数量 Number	变更描述/Description		签名 Signature	日期 Date	比例 Scale		版本 REV.	重量 Weight	数量 Qty.	产品料号 Part No.		1210040120001	
绘图 Drawn	YL YE	13.09.2018	标准件 Stand.	-	-	3:4	V1.1	14g	-	产品名称 Part Name		-		
审核 Checked	BQ LUO	13.09.2018												
工艺 Process	-	-	批准 Approved	HQ ZHANG	13.09.2018			All Dimensions in mm Original Size DIN A 4		厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD				