






P	LTR	DESCRIPTION	DATE	DNW	APVO
A	RELEASED		18SEP17	JL	IY



A-A



NOTES

- 1 THIS PART IS UL94 VO VERSION AND RELATED HB VERSION REFER TO TE DRAWING 2141155
- 2 PACKAGING: BULK PACKAGING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX

PART NO	DIM. A	FOR WIRE SIZE [mm ²]	MATERIAL	DESCRIPTION	WEIGHT (g)	SURFACE COLOR
2310488-3	12.6	25	PA66-GF UL94 VO	PROTECTION COVER	(3.3)	ORANGE
2310488-2	14.8	35	PA66-GF UL94 VO	PROTECTION COVER	(3.3)	ORANGE
2310488-1	16.2	50	PA66-GF UL94 VO	PROTECTION COVER	(3.3)	ORANGE

THIS DRAWING IS A CONTROLLED DOCUMENT. 12SEP2017
 DRAFTED BY: J.LI 15SEP2017
 CHECKED BY: C.JIANG 18SEP2017
 APPROVED BY: L.YIN
 NAME: PROTECTION COVER

DIMENSIONS: mm
 MATERIAL: SEE TABLE
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0.1 PL 0.3
 1.0 PL 0.5
 2.0 PL 0.5
 3.0 PL 0.5
 4.0 PL 0.5
 ANGLES: ±1°
 APPLICABILITY SPEC
 WEIGHT: -
 SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:
 A1 00779 C=2310488
 CUSTOMER DRAWING
 SCALE: 4:1 SHEET 1 OF 1 REV: A