



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: $\leq 20m\Omega$
- 1-3. 绝缘电阻: $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度: $+220^{\circ}C$, 10s max

三. 材质:

- 3-1. 塑胶: PBT(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

PIN	A	AI	B
3	13.40	12.20	4.00
4	15.40	14.20	6.00
5	17.40	16.20	8.00
6	19.40	18.20	10.00
7	21.40	20.20	12.00
8	23.40	22.20	14.00
9	25.40	24.20	16.00
10	27.40	26.20	18.00
11	29.40	28.20	20.00
12	31.40	30.20	22.00
13	33.40	32.20	24.00
14	35.40	34.20	26.00
15	37.40	36.20	28.00
16	39.40	38.20	30.00
17	41.40	40.20	32.00
18	43.40	42.20	34.00
19	45.40	44.20	36.00
20	47.40	46.20	38.00
21	49.40	48.20	40.00
22	51.40	50.20	42.00
23	53.40	52.20	44.00
24	55.40	54.20	46.00
25	57.40	56.20	48.00
26	59.40	58.20	50.00
27	61.40	60.20	52.00
28	63.40	62.20	54.00
29	65.40	64.20	56.00
30	67.40	66.20	58.00
31	69.40	68.20	60.00
32	71.40	70.20	62.00
33	73.40	72.20	64.00
34	75.40	74.20	66.00
35	77.40	76.20	68.00
36	79.40	78.20	70.00
37	81.40	80.20	72.00
38	83.40	82.20	74.00
39	85.40	84.20	76.00
40	87.40	86.20	78.00

	图名:	BX2.0-2xNA-5.6	未标注公差				绘制:	韩金锋	单位:	MM
			XX.	± 0.40	XX.°	$\pm 2^{\circ}$				
	图号:	XXXXXXXXXXXXXXXXXXXX	X.	± 0.30	.XX°	$\pm 1^{\circ}$	签发:		比例:	1:1
			.X	± 0.20						
		.XX	± 0.15							