






CAD FILE:

NOTES: Rating: 3A 250VAC
6A 125VAC



SCHEMATIC (NON-SHORTING)

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

P.C.B LAYOUT
BOTTOM VIEW

注: "*"表示关键尺寸 (4个).

8	CONTACT CLIP	PBS STRIP	2	Ag PLATED	TOLERANCE UNLESS SPECIFIED				
7	POSITION PLATE	STEEL STRIP	1	Ni PLATED					
6	STEEL BALL	STEEL	1	NATURAL	WITHIN 1.5mm : ±0.1mm	A	2012-8-4	初版	
5	SPRING	STEEL WIRE	1	NATURAL	OVER 1.5mm : ±0.2mm	ISSUE	DATE	DESCRIPTIONS OF REVISION	APPD.
4	TERMINAL	BRASS STRIP	6	Ag PLATED	TITLE : VERTICAL SLIDE SWITCH		UNIT : mm	DRWG NO.:	
3	BASE	PHENOLIC RESIN	1	NATURAL	MODEL: VS12-G15IBN-9		SCALF: ? · 1	DWN.	2012-8-4
2	FRAME	STEEL STRIP	1	Ni PLATED	东莞市六钧电子五金有限公司			CHK'D	2012-8-4
1	KNOB	POM	1	BLACK				APPD.	2012-8-4
NO.	PARTS	MATERIALS	Q'TY	FINISH					