



技术参数:

- 插芯:
- 插针数: 1
 - 额定电流: 200A
 - 额定电压: 1000V
 - 额定脉冲电压: 8kV
 - 污染等级: 3
 - 依据UL的额定电压: 600V
 - 绝缘阻抗: $>10^{10}\Omega$
 - 材料: 聚碳酸酯
 - 颜色: RAL 7032 (浅灰色)
 - 温度范围: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - 依据UL 94的阻燃等级: V0
 - 可插拔次数: ≥ 500
- 插针:
- 接线方式: 轴向螺栓连接
 - 材料: 铜合金
 - 表面处理: 镀银
 - 接触电阻: $<0.2\text{m}\Omega$
 - 线径范围: $25-40\text{mm}^2$
 - 内六角扳手: SW-5*150
 - 剥线长度: 16mm
 - 拧紧力矩:
- | | | | | |
|-------------------|----|----|----|----|
| · mm^2 : | 25 | 35 | 50 | 70 |
| · N·m: | 8 | 8 | 9 | 10 |

Technical specification:

- Insters:
- No. of contact: 2
 - Rated current: 200A
 - Rated voltage: 1000V
 - Rated impulse voltage: 8kV
 - Pollution degree: 3
 - Rated voltage acc.to UL: 600V
 - Insulation resistance: $>10^{10}\Omega$
 - Material: polycarbonate
 - Colour: RAL 7032(light grey)
 - Temperature range: $-40^{\circ}\text{C} - +125^{\circ}\text{C}$
 - Flammability acc.to UL 94: V0
 - Mating cycles: ≥ 500
- Contacts:
- Terminal: axial screw terminal
 - Material: copper alloy
 - Surface: hard-silver plated
 - Contact resistance: $\leq 0.2\text{m}\Omega$
 - Wire gauge: $25-40\text{mm}^2$
 - Hexagonal driver: SW-5*150
 - Stripping length: 16mm
 - Tightening torque:
- | | | | | |
|-------------------|----|----|----|----|
| · mm^2 : | 25 | 35 | 50 | 70 |
| · N·m: | 8 | 8 | 9 | 10 |

						表面处理 Finish		-		图号 Drawing No.	-
						材料 Material		-		产品代号 Part Code	H2MKPE-001.1-M
标记 Mark	处数 Number	变更描述/Description			签名 Signature	日期 Date			产品料号 Part No.		1290010110001
绘图 Drawn	BQ LUO	姓名/Name	日期/Date	姓名/Name	日期/Date	比例 Scale	版本 REV.	重量 Weight	数量 Qty.	产品名称 Part Name	-
审核 Checked	P RAO		18.10.2010	-	-	1:1	V1.0	95.5g	-		
工艺 Process	-		-	批准 Approved	YY LIN	18.10.2010	All Dimensions in mm Original Size DIN A 4		厦门唯恩电气有限公司 XIAMEN WAIN ELECTRICAL CO.LTD		