





NOTES:
 1. Rating : 16A GP 125/250VAC 5E4 40T125
 16(4)A 125/250VAC 5E4 40T125
 16A 42VDC 5E4 40T125
 2. Contact resistance : 50m Ω Max
 3. Insulation resistance : >100M Ω (Min) 500VDC
 4. Dielectric strength : >1500VAC 0.5mA 1 minutes



电话: 0769-82310511-867
 邮箱: hooya89@hooya.hk

NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	DIMENSIONAL TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
5	4	3	2	1	RANGE	TOLERANCE					SCALE	NO	DRAWING NO.	REV.
10	9	8	7	6	X	± 0.30					MAT'L	***		
					X.X	± 0.20					MATERIAL NO.		RT-M1-1C3B16A050	
					X.XX	± 0.10							*****	A
						$\pm 1'$								

LMC
2019.05.15

LEGION ELECTRONIC & HARDWARE CO., LTD.

A

A

4

3

2

1