







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	20MAR2015	DW	CW
	B	ECR-15-018270	07DEC2015	DW	CW
	B1	ECR-17-003902	16APR2017	RL	CW
	C	ECR-21-111798	23SEP2021	WQR	CW



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 830V
RATED CURREN3T: 40A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40^{\circ}C \sim +125^{\circ}C$
WIRE RANGE: $1.5mm^2 \sim 6.0mm^2$
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20400X20XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 830V
额定电流: 40A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40^{\circ}C \sim +125^{\circ}C$
接线范围: $1.5mm^2 \sim 6.0mm^2$
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20400X20XX000)

T2111042201-000	HMN-004-F	HMN-004 FEMALE MODULE INSERT HMN-004模块母插
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 20MAR2015	TE Connectivity HMN-004-F		
		CHK Chris.Wang 20MAR2015			
		APVD Xiang.Xu 20MAR2015			
		PRODUCT SPEC 108-137060			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL		FINISH			
-		-	A300779C-T2111042201000		
-		-	Customer Drawing		
			SCALE 3:2	SHEET 1 OF 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2111042201-000](#)