
#### 4-40 THREAD






CAT. NO. 612

MATERIAL:

.062 (1.57) Steel, Zinc Plate

## 4-40 THREAD






CAT. NO. 621

MATERIAL: .062 (1.57) Steel, Zinc Plate

#### 4-40 THREAD






CAT. NO. 616

**MATERIAL:** 

.047 (1.19) Brass, Tin Plate

### 6-32 THREAD






CAT. NO. 634

**MATERIAL:** 

.032 (.81) Brass, Nickel Plate

#### 6-32 THREAD






CAT. NO. 614

MATERIAL:

.032 (.81) Brass, Tin Plate

### 6-32 THREAD






**CAT. NO. 632** 

**MATERIAL:** .032 (.81) Brass, Tin Plate

### 6-32 THREAD






CAT. NO. 4334

**MATERIAL:** 

.062 (1.57) Steel, Nickel Plate

# 6-32 THREAD




**CAT. NO. 708** 

**MATERIAL:** .062 (1.57 Steel, Nickel Plate

### 6-32 THREAD






CAT. NO. 617

**MATERIAL:** .062 (1.57) Steel, Tin Plate

### 6-32 OR 8-32 THREAD






CAT. NO. THREAD 4332 6-32

MATERIAL: .062 (1.57) Brass, Nickel Plate

#### 8-32 THREAD






CAT. NO. 611

.037 (.94) Brass, Tin Plate

#### 8-32 THREAD





CAT. NO. 631

.037 (.94) Steel, Tin Plate

**MATERIAL:** 

KEYSTONE Rohs Compliant - ISO 9001 CERTIFIED