

E		F	
修 订	标 记	修 改 描 要	签 名
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE
		NEW DWG	
			日期 DATE
			2016-03-12

规格说明:Specifications:

电气特性:Electrical:

- 1. 额定电流: Current Rating
1.5A/contact terminal
- 2. 额定电压: Voltage Rating
30V DC
- 3. 接触阻抗:Contact Resistance
30 milliohms MAX
- 4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
- 5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:


- 1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
- 2. 端子保持力: Terminal Retenion
1.2kgf (MIN)

原材料:Material:

- 1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
PBT
- 2. 端子:Contact:Copper Alloy C2680
- 3. 外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

- 1. 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
- 2. 外壳:Shell:
Nickel Plating



		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-23304126 传真: 0755-29940187					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 		TITLE: USB AF90度沉板弯脚平口黑胶 产品名称: PBT0.25			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: USB-ZD-119DIP		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm
							CODE NUMBER A001