






PCB LAYOUT BOTTOM VIEW





SCHEMATIC (SHORTING)

1. Specification:

1. 规范:
2. Rating: 1.0A/DC24V
3. 额定值: 1.0A/DC24V
4. Contact resistance: $\leq 50\text{m}\Omega$
5. 接触电阻: $\leq 50\text{m}\Omega$
6. Insulation Resistance: $\geq 100\text{M}\Omega$ DC250V
7. 绝缘电阻: $\geq 100\text{M}\Omega$ DC250V
8. Compressive strength: AC250V 1minute
9. 抗压强度: AC250V 1分钟

6. Operating temperature: -25°C to $+70^{\circ}\text{C}$

6. 工作温度: -25°C 至 $+70^{\circ}\text{C}$
7. Storage humidity: $<85\%\text{RH}$
8. 储存湿度: $<85\%\text{RH}$
9. Electrical life: 10,000 Cycles
10. 电气寿命: 10000次
11. Operating Force: $260 \pm 80\text{gf}$
12. 操作力: $260 \pm 80\text{gf}$



7	STEEL BALL 钢珠	STEEL	1	NATURAL
6	SPRING PLATE 簧片	STEEL WIRE	1	TEMPER
5	CONTACT CLIP 接触片	PBS STRIP	4	Ag CLAD
4	TERMINAL 端子	BRASS	12	Ag PLATED
3	BASE 基座	PHENOLIC RESIN	1	NATURAL
2	FRAME 框架	STEEL	1	Ni PLATED
1	KBOB 手柄	PA66	1	BLACK
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP60421124
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				