





PCB LAYOUT BOTTOM VIEW
PCB布局底视图

- | | |
|---|---|
| 1. Specification: | 6. Operating temperature: -25℃ to + 70℃ |
| 1. 规范: | 6. 工作温度: -25℃至 + 70℃ |
| 2. Rating: 1.0A/DC24V | 7. Storage humidity: <85%RH |
| 2. 额定值: 1.0A/DC24V | 7. 储存湿度: < 85%RH |
| 3. Contact resistance: ≤50mΩ | 8. Electrical life: 10,000Cycles |
| 3. 接触电阻: ≤50mΩ | 8. 电气寿命: 10000次 |
| 4. Insulation Resistance: ≥100MΩ DC250V | 9. Operating Force: 260±80gf |
| 4. 绝缘电阻: ≥100MΩDC250V | 9. 操作力: 260±80gf |
| 5. Compressive strength: AC250V 1minute | |
| 5. 抗压强度: AC250V 1分钟 | |

6	Contact strip 接触片	BRASS 黄铜	2	Ag PLATED 镀银
5	SPRING 弹簧	SUS 不锈钢	2	
4	TERMINAL 终端	BRASS 黄铜	6	Ag PLATED 镀银
3	BASE 基座	PHENOLIC RESIN 酚醛树脂	1	
2	FRAME 框架	Iron 铁	1	Ni PLATED 镀镍
1	KNOB 手柄	PA66	1	BLACK 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: SK-22F14-6
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X					
						ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission			
A		B		C		D	E	F	G		