



- Technical requirements:
技术要求:
- 1.Service life: 700000 times min
1.寿命: 700,000次
 - 2.Contact impedance: 100M ohm max
接触阻抗: 100M ohm max
 3. Insulation impedance: 1000m ohm / 100V DC min
3.绝缘电阻: 1000m ohm / 100V DC min
 4. Withstand voltage: AC250V (50Hz or 60Hz) / 60sec
4.耐电压: AC250V (50Hz or 60Hz) / 60sec
 5. Heat resistance: 85 ± 2 ° C, 96h
5.耐热性: 85 ± 2 ° C, 96h
 6. Service temperature: - 40 ~ + 85 ° C
6.工作温度: 40 ~ + 85 ° C
 - 7.Moisture resistance: 40 ± 2 ° C, humidity 90% ~ 95%, 504h
7.抗湿性: 40±2°C, 湿度90%~95%, 504H
 8. Salt spray test: 48h
8.盐雾测试: 48H
 - 9.Conduction stroke: 0.25mm ~ 0.45mm
9.导通行程: 0.25mm~0.45mm
 - 10.Action force: 160±50gf
10.动作力: 160±50gf

5	terminal 端子	Phosphor copper 磷铜	4	silver/0.8um Min 镀银/0.8um Min
4	Base 底座	PA6T 尼龙6T	1	
3	Shrapnel 弹片	SUS 不锈钢	1	silver/0.8um Min 镀银/0.8um Min
2	membrane 膜片	Kapton tape	1	
1	Cover plate 盖板	SUS 不锈钢	1	
Project 项目	Spare parts 零件	texture of material 材质	Quantity 数量	remarks 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP40223216
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
ROCPU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				