





SCHEMATIC



PCB LAYOUT

Main Specifications
 Climate grade:-30℃~ + 80℃
 Rated values: Max50 mA12V DC
 Min10 uA12V DC
 Contact resistance:≤100mΩ
 Dielectric strength: 100V,AC,1Min
 Insulation resistance:≥100MΩ
 Operating force: 260±50g
 Travel: 0.22±0.05mm
 Life: 100,000 times



5	Protective film	PA	1	white
4	Press handle	PA	1	Black
3	Shrapnel	SUS301-EH Ag	2	Silver
2	base	PA	1	Black
1	Pin	Phosphor copper	1	Silver
ITEM	Name	Materials	NUM	COLOR

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP40121126	
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					
					X	± 0.25						
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					