






| 修订<br>REV | 标记<br>MARK | 修改摘要<br>REVISION DESCRIPTION | 签名<br>SIGNATURE | 日期<br>DATE |
|-----------|------------|------------------------------|-----------------|------------|
| A0        |            | NEW RELEASE                  | 黄艳兰             | 2013-06-11 |
|           |            |                              |                 |            |



| PIN | 尺寸 (mm) |       |
|-----|---------|-------|
|     | A       | B     |
| 2P  | 3.96    | 7.92  |
| 3P  | 7.92    | 11.88 |
| 4P  | 11.88   | 15.84 |
| 5P  | 15.84   | 19.80 |
| 6P  | 19.80   | 23.76 |
| 7P  | 23.76   | 27.72 |
| 8P  | 27.72   | 31.68 |
| 9P  | 31.68   | 35.64 |
| 10P | 35.64   | 39.60 |
| 11P | 39.60   | 43.56 |
| 12P | 43.56   | 47.52 |
| 13P | 47.52   | 51.48 |
| 14P | 51.48   | 55.44 |
| 15P | 55.44   | 59.40 |
| 16P | 59.40   | 63.36 |

## 技术要求

- 温度范围 (Temperature range):  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 额定电压 (Voltage rating): 250V.AC/DV
- 额定电流 (Current rating): 7.5A
- 接触电阻 (Contact resistance):  $\leq 0.02\ \Omega$
- 绝缘电阻 (Insulation resistance):  $\geq 1000\text{M}\Omega$
- 耐压 (Withstand voltage): 1000V.AC/1分钟 (Minute)



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD  
TEL: 0755-27111225 FAX: 0755-29940187

| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED<br>公差参数表 |       |        |     | TITLE:<br>产品名称: VH3.96弯针 |                                 |       |      |
|-----------------------------------------------------|-------|--------|-----|--------------------------|---------------------------------|-------|------|
| X.X                                                 | ±0.30 | X.X°   | ±3° | APPD:<br>核准:             | PART NO:<br>产品编号: HDGC3963WR-XP |       |      |
| X.XX                                                | ±0.30 | X.XX°  | ±2° | CHECK:<br>校对: 王建业        | DATE                            | SCALE | UNIT |
| X.XXX                                               | ±0.10 | X.XXX° | ±1° | DRAW:<br>绘图: 黄艳兰         | 2013-06-11                      | 1:1   | mm   |
|                                                     |       |        |     | CODE NUMBER<br>A126      |                                 |       |      |