






RECOMMENDED PCB LAYOUT
安装尺寸图



CIRCUIT DIAGRAM
回路图



LAND PATTERN PLAN
电路板焊盘参考图

Specifications

规格

Rating: DC12V 50mA

额定负荷: DC12V 50mA

Contact Resistance: 500mΩ max

接触电阻: 500mΩ max

Insulation resistance: DC100V 60S 100MΩ min

绝缘电阻: DC100V 60S 100MΩ min

Dielectric strength: AC250V(50~60HZ)60S min

抗电强度: AC250V(50~60HZ)60S min

Operation force: 260±50gf

操作力: 260±50gf

Operating Life: 500,000 cycles

寿命: 500,000 cycles

Travels: 0.12±0.05mm

行程: 0.12±0.05mm

Operating Temperature range: -40°C ~ +90°C

使用温度范围: -40°C ~ +90°C

Waterproof grade: IP67

防水等级: IP67

5	Knob 按钮	POLYAMIDE 尼龙	1	BLACK 黑色
4	FILM 胶片	POLYAMIDE 尼龙	1	WHITE 白色
3	Shrapnel 弹片	STAINLESS STEEL 不锈钢	2	Ag-PLATED 镀银的
2	Pedestal 基座	POLYAMIDE 尼龙	1	BLACK 黑色
1	TERMINAL 端子	PHOSPHOR BRONZE 磷青铜	1	Ag-PLATED 镀银的
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25

ANGULAR

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP40321126
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				