


SFV CONNECTOR



2.0mm pitch/Disconnectable Crimp style connectors



This SFV connector is a wire-to-board connector for connecting power supply and PCB and withstands high voltage. It is used for power supply of LED backlight in Liquid Crystal Display Television set.

- Withstand high voltage
- Secure locking structure
- Halogen-free

Specifications –

- Current rating: 1.0 A AC, DC (AWG #28)
- Voltage rating: 300 V AC, DC
- Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)

• Contact resistance: Initial value/ 20 m Ω max.


After environmental tests/ 40 m Ω max.


- Insulation resistance: 1,000 M Ω min.
- Withstanding voltage: 1,700 VAC/minute
- Applicable wire: Conductor size/ AWG #30 to #28 Insulation O.D./ 0.8 to 0.92 mm
- * Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.
- * Contact JST for details.
- * Compliant with RoHS.

Standards -

Recognized E60389

PC board layout and Assembly layout






Note: 1. The above figure is the figure viewed from the connector mounting side.

2. Tolerances are non-cumulative: ± 0.05 mm for all centers. The dimensions above should serve as a guideline. Contact JST for details.

Contact



| Model No. | Applicable wire | | Insulation O.D. (mm) | O'ty/rool |
|----------------|-----------------|----------|-------------------------|-----------|
| | mm ² | AWG# | insulation O.D. (IIIII) | Q ty/reer |
| SGVH-002T-P0.2 | 0.05 to 0.08 | 30 to 28 | 0.8 to 0.92 | 23,000 |

Material and Finish

Phosphor bronze, tin-plated (reflow treatment)


RoHS compliance

| | Crimping | | | |
|----------------|----------|------------------|----------------|----------------------------|
| Contact | machine | Crimp applicator | Dies | Crimp applicator with dies |
| SGVH-002T-P0.2 | AP-K2N | MKS-L-10-3 | MK/SSHL-002-02 | APLMK SSHL002-02 |
| | | _ | _ | _ |

Note: Contact JST for fully automatic crimping applicator.

SFV CONNECTOR


Housing



| No. of circuits | Model No. | Q'ty/bag | | | |
|-----------------|-----------------------|----------|--|--|--|
| 2 | SFVR-02V-S(HF) | 2,000 | | | |
| Material | | | | | |
| | PBT, UL94V-0, natural | | | | |

RoHS compliance

Header



| No. of circuits | Model No. | Q'ty/reel |
|-----------------|---------------------|-----------|
| 2 | BM02B-SFVH-TF(HF) | 2,000 |
| | Material and Finish | |


Contact: Phosphor bronze, copper-undercoated, tin-plated (reflow treatment) Housing: Modified PA 6T, UL94V-0, gray

RoHS compliance


Note: The product listed above is supplied on embossed-tape.

Model number allocation

Contact



Housing



Header

