


JFA CONNECTOR METALSHELLSERIES

Wire-to-wire connector (For Interface)



Metal shell type I/O connector which contacts are used also with JFA connector J2000 series and J300 series.

- · Applicable contact and tooling can be unified
- · Rigid metal shell
- Waterproof performance
- Misinsertion prevention

- * In using the products, refer to "Handling Precaution for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.

JFA CONNECTOR/METAL SHELL SERIES


Line-up of metal shell


♦J2900

Connector series	J2000 series 40P
J2900	
No. of circuits	20P × 2 pcs.

♦JFA-M


Туре	Shell	Examples of combinations			
		J2000 (22P) × 2	J2000 (22P) ×1+J300 (12P) ×1	J300 (12P) × 2	
2 Module					
No. of circuits		44P	34P	24P	







JFA CONNECTOR J2900 SERIES



This connector is a metal shell type I/O connector and it's completely waterproof. Contacts are designed to be common use with JFA connector J2000 series.

- · Rigid metal shell
- · Easy mating operation

■ Standards

Recognized E 60389

△ : R 50354834

■ Specifications

· Current rating: 3 A AC/DC (AWG #20)

· Voltage rating: 250 V AC/DC

· Temperature range: -55°C to + 105°C

(including temperature rise in applying


electrical current)

 \cdot Applicable cable O.D.: 11.1 to 13.5 mm

- * Please note that the above general specifications may differ from the safety standards.
- * In using the products, refer to "Handling Precaution for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.


METAL SHELL SERIES / J2900

Receptacle housing assembly



No. of circuits	Model No.	Q'ty/box	
20	J29FA-20-K	70	

RoHS2 compliance




No. of circuits	Model No.	Q'ty/box
20	J29FA-20-H-1	70

RoHS2 compliance


METAL SHELL SERIES /J2900

Tab housing assembly



No. of circuits	Model No.	Q'ty/box
20	J29MA-20-K	70

RoHS2 compliance




No. of circuits	Model No.	Q'ty/box
20	J29MA-20-H-1	70

RoHS2 compliance

METAL SHELL SERIES / J2900

◆ Wire side

Shell kit



● For Pg21		
	(40.2)	
(Pg21)	(10)	
Pg21 screw	mounting product (For flexible tubing, etc.)	

Model No.	Q'ty/box
J29WK-K-1	30


RoHS2 compliance This product displays (PF) on a label.

Model No.	Q'ty/box
J29WK-K-A	35

RoHS2 compliance This product displays (PF) on a label.


◆ Panel side

Shell kit



Model No.	Q'ty/box
J29PK-K	35

RoHS2 compliance This product displays (PF) on a label.




Model No.	Q'ty/box	
L3.5-R4	1,000	

RoHS2 compliance



JFA CONNECTOR JFA-M SERIES



Metal shell type connector which contacts are designed to be common use with JFA connector J2000 series and J300 series.

- · Rigid metal shell
- Lever (3 and 4 module types) provides easy mating and unmating connector
- · Combination of modular housing

■ Standards

Recognized E 60389

△: R50287698

Specifications

· Current rating: J2000 Series (2 and 3 Module)

...3 A AC/DC (AWG #20)

J2000 Series (4 Module)

...2.5 A AC/DC (AWG #20)

J300 Series ...5 A AC/DC (AWG #16)

Voltage range: J2000 Series …250 V AC/DC

J300 Series ···600 V AC/DC

· Temperature range: -55°C to +105°C

(including temperature rise in applying

electrical current)


- Please note that the above general specifications may differ from the safety standards.
- * In using the products, refer to "Handling Precaution for Terminals and Connectors" described on our website (Technical documents of Product information page).
- * RoHS2 compliance
- * Dimensional unit: mm
- * Contact JST for details.

METAL SHELL SERIES / JFA-M

Components


◆ Wire side

Shell assembly




◆ Panel side

Shell assembly




Examples of use


Waterproof I/O connector




Drawer type



Drawer type (Rack mounting method)




J2000 series housing (User for both panel mounting and drawer type)



RoHS2 compliance


J300 series housing (User for both panel mounting and drawer type)



RoHS2 compliance

METAL SHELL SERIES/JFA-M


◆ Wire side



No. of	Model No.	Model No Applicable Cable O.D.	Dimensions (mm)		
combining housing	Model No.	(mm)	Α	В	С
3 Module	JFM-WSA-3-B	φ 20.2 to 22.0	95.0	70.5 82.0	90.0
3 Module	JFM-WSA-3-C	φ 15.5 to 16.5	95.8		02.0
4 Madula	JFM-WSA-4-A	φ 26.2 to 28.0	103.5	79.0	99.0
4 Module	JFM-WSA-4-C	φ 15.5 to 16.5	104.3	79.0	

No.	Parts name	Q'ty
1	Wire side shell	1
2	Seal ring	1
3	Clamp nut	1
4	Clamp rubber	1

RoHS2 compliance This product displays (PF) on a label.




	No. of	Model No.	Di	imension (m	m)
(conbining housing	WIOGEI IVO.	Α	В	С
	2 Module	JFM-WSA-2-1	18.0	64.0	66.2
		5 .		0.1	
	No.	Part name		Q'	ty
	1	Wide side shell			1
_	2	Seal ring			1

RoHS2 compliance

◆ Panel side

Shell assembly




No. of	Model No.	1	Dimensio	ns (mm)	
combining housing	Model No.	Α	В	С	D
2 Module	JFM-PSA-2	60.5	59.7	69.0	81.5
3 Module	JFM-PSA-3	60.6	76.7	86.0	98.5
4 Module	JFM-PSA-4	60.6	93.7	103.0	115.5

No.	Parts name	Q'ty
1	Panel side shell	1
2	Seal rubber prate	1

RoHS2 compliance JFM-PSA-3 and JFM-PSA-4 display (PF) on a label.

Guide plate A (With the combination of side and panel side shell assembly)



No. of	Model No.		Dime	ensions	(mm)	
combining housing	woder No.	Α	В	С	D	E
2 Module	JFM-GPAK-2	9.6	37.4	46.0	54.8	41.9
3 Module	JFM-GPAK-3	9.7	54.4	63.0	72.0	41.4
4 Module	JFM-GPAK-4	9.7	71.4	80.0	89.0	41.4

No.	Parts name	Q'ty
1	Guide plate A assembly	1
2	Washer assembly screw	4
3	Guide pin A JFM-PIA3-N	_
4	Guide pin B JFM-PIB3-N	_


RoHS2 compliance
Note: Guide pins A and B are optional parts.

Refer to the combinations list below for the guide pin A/B usage. (Shell mounting pattern at panel side)

No. of guide pins	Pattern 1	Pattern 2	Pattern 3	Pattern 4	Pattern 5	Pattern 6
Guide pin A: 0 pcs. Guide pin B: 4 pcs.						
Guide pin A: 1 pcs. Guide pin B: 3 pcs.	- -	- -	- -	- -		
Guide pin A: 2 pcs. Guide pin B: 2 pcs.	- - - - - -	- -	- -	- -	- -	
Guide pin A: 3 pcs. Guide pin B: 1 pcs.	- -		- -	- -		
Guide pin A: 4 pcs. Guide pin B: 0 pcs.						

Note: Shell mounting pattern at wire side becomes opposite to the above pattern.


Panel cut dimensions



No. of	Dimensions (mm)			
combining housing	Α	В	С	
2 Module	60.0	69.0	46.4	
3 Module	76.9	86.0	46.3	
4 Module	93.9	103.0	46.3	

METAL SHELL SERIES / JFA-M

Guide plate B




No. of	Model No.	Dir	mensions (r	nm)
combining housing	woder No.	Α	В	С
3 Module	JFM-GPBK-3	54.4	63.0	72.0
4 Module	JFM-GPBK-4	71.4	80.0	89.0


No.	Parts name	Q'ty
1	Guide plate B Assembly	1
2	M4 stepped screw	4

RoHS2 compliance

Drawer type rack panel cut dimensions



No. of	Г	Dimensions (mm)
combining housing	Α	В	С
3 Module	56.2	63.0	69.0
4 Module	73.2	80.0	86.0



No. of	Dimensions (mm)			
combining housing	Α	В	С	
3 Module	57.1	63.0	73.0	
4 Module	74.1	80.0	90.0	