



Recommended PCB Layout(Top view)
Tolerance:±0.05mm

Specifications:

规格:

- Voltage rating:250V AC/DC
- 额定电压: 250V AC/DC
- Current rating 24A AC/DC
- 额定电流: 24A AC/DC
- Withstanding voltage:1000V AC/minute
- 耐受电压: 1000V AC/分钟
- Temperature range:-40°C~+105°C
- 温度范围: -40°C~+105°C
- Insulation resistance:≥1000MΩ
- 绝缘电阻: ≥1000MΩ
- Contact resistance:≤20mΩ
- 接触电阻: ≤20mΩ

X9396 W R - XX R - LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Straight 90°
- 4.Row No.Pin No:XX-02~2x08Pin
- 5.Special No:R-DIP 2.2mm
- 6.Material:LP-LCP UL94V-0 ,Natural
- 7.Plating:SN- Tin Plated

| Poles | Dimensions (mm) | | |
|-------|-----------------|-------|-------|
| | A | B | C |
| 02 | 3.96 | 7.92 | 5.32 |
| 03 | 7.92 | 11.88 | 9.28 |
| 04 | 11.88 | 15.84 | 13.24 |
| 05 | 15.84 | 19.80 | 17.20 |
| 06 | 19.80 | 23.76 | 21.16 |
| 07 | 23.76 | 27.72 | 25.12 |
| 08 | 27.72 | 31.68 | 29.08 |

| | | | |
|------------------|----------|---------------|----------------------|
| X9396WR-XXR-LPSN | LCP | Brass | X9396H |
| PART NO | Material | Material(Pin) | Suitable XKB Housing |

| | | | |
|------|--|-------------|---|
| DSND | | SCALE: N/A | MODEL TYPE: 3.96mm Crimp Style Connector |
| DWN | | VIEW: | PART NO.: X9396WR-XXR-LPSN |
| CHKD | | UNIT: mm/in | DWG NO.: X-X9396WR-XXR-LPSN |
| APPD | | SIZE: A4 | |



XKB INDUSTRIAL PRECISION CO.,LIMITED

| | | |
|--------|-------|----------|
| WEIGHT | SHEET | REVISION |
| | 1/1 | A0 |

广东星坤科技股份有限公司

| | |
|----|----|
| 作 | 日期 |
| 日期 | |

文件工程章

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|------|-------------|------|---------|----------|------------------------|
| | REVISIONS | | | | |
| | | | | | ANGULAR ±5° |
| | | | | | L ≤ 4 ±0.2 |
| | | | | | 4 < L ≤ 16 ±0.3 |
| | | | | | 16 < L ≤ 63 ±0.4 |
| | | | | | L > 63 ±0.5 |

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn