



Specifications:


规格:

- Voltage rating: 250V AC/DC
- 额定电压: 250V AC/DC
- Current rating: 24A AC/DC
- 额定电流: 24A AC/DC
- Withstanding voltage: 1000V AC/minute
- 耐受电压: 1000V AC/分钟
- Temperature range: -40°C~+105°C
- 温度范围: -40°C~+105°C
- Insulation resistance: ≥1000MΩ
- 绝缘电阻: ≥1000MΩ
- Contact resistance: ≤20mΩ
- 接触电阻: ≤20mΩ



X9396 W V - XX R - LP SN
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: V-Straight 180°
4. Row No. Pin No: XX-02~2x08Pin
5. Special No: R-DIP 2.2mm
6. Material: LP-LCP UL94V-0 ,Natural
CAP: LCP UL94V-0 ,Natural
7. Plating: SN- Tin Plated



Recommended PCB Layout(Top view)
Tolerance: ±0.05mm

Poles	Dimensions (mm)		
	A	B	C
02	3.96	7.92	5.32
03	7.92	11.88	9.28
04	11.88	15.84	13.24
05	15.84	19.80	17.20
06	19.80	23.76	21.16
07	23.76	27.72	25.12
08	27.72	31.68	29.08

X9396WW-XXR-LPSN	LCP	Brass	X9396H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 3.96mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9396WW-XXR-LPSN
CHKD	UNIT: mm/in	DWG NO.: X-X9396WW-XXR-LPSN
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

MARK	DESCRIPTION	DATE	REVISED	APPROVED
	REVISIONS			

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

广东星坤科技股份有限公司

文件工程章