



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:NYLON BLACK UL94V-0

b.CONTACT:STEEL

(SURFACE PLATING: Au 1U")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

b.OPERATING TEMPERATURE: -10° C~ +80° C

ORDERING INFORMATION

BH-AA-B***015

电池盒

电池型号

SMT 180° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN






3B-PPS BLACK

4A-LCP WHITE

4B-LCP BLACK

5A-PA9T BLACK

5B-NYLON BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2020-05-13
		CHKD	ZhouRuicai	DATE	2020-05-13
		APVD	XueShunyong	DATE	2020-05-13
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊕ ⊞
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	TITLE: 电池盒BH-AA-2J Au SMT
		PART NO.:		BH-AA-B5BA015	
		DRAW NO.:		MY-CP-0122	

2	TERMINAL	4	STEEL, T=0.3mm	Au-Plating
1	HOUSING	1	NYLON 94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR