



由Autodesk教育版产品制作



PCB板孔位



修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12

规格说明:Specifications:

电气特性:Electrical:

- 额定电流: Current Rating
1.5A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗:Contact Resistance
30 milliohms MAX
- 耐电压:Dielectnc Withstanding Voitage:
500 V AC AT Sea Levcl
- 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 插拔力: Cnnector Mate and Unmate Force
Mate force:3.75kgf (MAX)
Unmate force:1.02kgf (MIN)
- 端子保持力: Terminal Retenion
1.2kgf (MIN)

原材料:Matarial:

- 塑胶:Housing:
Hing Temperature Tnermaplastics,
U1 94V-0 PBT/LCP White/Black
- 端子:Contact:Copper Alloy C2680
- 外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

- 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
- 外壳:Shell:
Nickel Plating



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: USB AM180度弯脚有柱LCP黑胶	
X.X	± 0.30	X.X*	$\pm 3^\circ$
X.XX	± 0.20	X.XX*	$\pm 2^\circ$
X.XXX	± 0.10	X.XXX*	$\pm 1^\circ$

APPD: 核准:	CHECK: 校对: 王建业	PART NO: 产品编号: USB-ZL-106PWB	DATE	SCALE	UNIT	CODE NUMBER
DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001		

由Autodesk教育版产品制作