







PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X9555 W V S-2xXXE- PT-XXXX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:V-180°

4.Welding Way:S-SMT

5.Row No-Pin No:2xXX-Double Row

6.Plug the Pin&Special NO:

E-Matching 9555H-2xXXE HSG

7.Material:PT-PBT 94V-0

9T-PA9T 94V-0

8.Plating Category:

VXX-All Gold-Plated X01-Gold Flash

X05-Gold:5u" SN-Bright Tin Plating(70u")

9.Color:Blank-Natural Color

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
06	5.08	10.12	8.12	24	27.94	32.98	30.98
08	7.62	12.66	10.66	26	30.48	35.52	33.52
10	10.16	15.20	13.20	28	33.05	38.06	36.06
12	12.70	17.74	15.74	30	35.56	40.60	38.60
14	15.24	14.00	18.28	32	38.10	43.14	41.15
16	17.78	20.28	20.82	34	40.64	45.68	43.68
18	20.32	25.36	23.36	36	43.18	48.22	46.22
20	22.86	27.90	25.90	38	45.72	50.76	48.76
22	25.40	30.44	28.44	40	48.26	53.30	51.30

X9555WVS-2xXXE-9TV05	PA9T UL 94V-0	Brass	Gold:5U"	X9555H
X9555WVS-2xXXE-PTSN	PBT UL 94V-0		Tin-Plated	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生		日期
效		
ΔX		
ΔX		
ΔX		
MARK	文件工程章	

DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

units: mm
tolerance:
X.X ±0.2mm
X.XX ±0.1mm
X.XXX ±0.05mm

UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	2.54mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.: X9555WVS-2xXXE-XXXX
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0