




**RoHS**  
Compliant  
2011/65/EU






REV.	ECN NO OR DESCRIPTION	REVISED	DATE


A



SECTION: A-A





WITHDRAW CARD	INSERT CARD
GROUND PIN (C5) □ Switch Pin (S/W)	GROUND PIN (C5) □ Switch Pin (S/W)



RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

## NOTES:

1. ELECTRICAL CHARACTERISTICS
  - 1-1. CONTACT RESISTANCE: 60 Milliohms Max
  - 1-2. INSULATION RESISTANCE: 1,000 Megohms Min.
  - 1-3. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE.
2. MECHANICAL CHARACTERISTICS
  - 2-1. OPERATION TEMPERATURE RANGE: -25°C~+70°C
  - 2-2. DURABILITY: 5000 CYCLES
3. MATERIAL:
  - 3-1. HOUSING: THERMOPLASTIC,UL 94-V0
  - 3-2. TERMINAL: PHOSPHOR BRONZE,T=0.15
  - 3-3. SHELL: STAINLESS STEEL,T=0.15
4. FINISHED:
  - 4-1. TERMINAL: NI PLATED UNDER,Au PLATED ON CONTACT AREA,G/F PLATED ON SOLDERTAIL



UNLESS OTHERWISE  
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD


DECIMALS:	ANGLES:	TITLE	MICRO SIM 撤盖式 1.5H带侦测
X :±0.50	X :±2°	DWN	xiong PART NO. SNO-1340-P9
X.X :±0.25	X.X :±1°	CHKD	lee SCALE:1:1 UNIT: mm
X.XX :±0.12		APVD	wang SIZE: A4 SHEET:1OF 1 REV: A4

CUSTOMER COPY

SIM CARD	
Pin No.	NAME
C1	VCC
C2	RST
C3	CLK
C4	RESERVED
C5	GND
C6	VPP
C7	I/O
C8	RESERVED
S/W	Switch Pin



RoHS  
Compliant  
2011/65/EU



3REE


44.5

上带剥离力方向

剥离角度165°~180度

载带拉出方向

SEE VIEW A



VIEW A(X2)


载带收料方向



前端卷入空下带45格

中间包装产品1300PCS

尾端卷入空下带5格



PULL OUT DIRECTION 拉出方向

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

## PACKING NOTES:

1. PRIMARY PACKING: 1300PCS/REEL;
2. SECONDARY PACKING: 10 REELS/CARTON (13KPCS/CARTON)
3. PEELING RESISTANCE: 30gf~100gf
4. PEELING ANGLE: 165°~180°
5. PEELING SPEED: 300mm/minutes.




TABLE:

NO.	NAME	SPEC.	REMARK
①	成品	掀盖 MICRO SIM CARD 1.5H	1300PCS/R
②	下带(载带)	PET料 透明色, W=24mm, P=20mm, T=0.3mm,	26.6M/1300PCS
③	上带(盖带)	W=21.5mm, T=0.06mm, 自粘式透明状	26.8M/1300PCS
④	REEL(蓝色卷盘)	外直径330mm, 内直径100mm, 内宽44.5mm	1PCS/1300PCS
⑤	折叠板	296*464*6mm	4PCS/14300PCS
⑥	CARTON (外箱)	350*350*350mm	1PCS/14300PCS

UNLESS OTHERWISE  
SPECIFIED TOLERANCES东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	MICRO SIM 掀盖式 1.5H带侦测
X :±0.50	X :±2°	DWN	xiong
X.X :±0.25	X.X :±1°	CHKD	lee
X.XX :±0.12		APVD	wang
		SIZE: A4	SCALE:1:1
		UNIT: mm	UNIT: mm
		SHEET:10F	REV: A4
			CUSTOMER COPY