


D

9	LOCK	1PC	SUS304	Clean
8	Pin PIN	1PC	C5191	Contact gold flash plating ;solder plating gold flash
7	SW PIN	1PC	C5191	Contact gold flash plating ;solder plating gold flash
6	SLIDER	1PC	E473I 30%G.F	UL94V-0; Color BLACK
5	SPRING	1PC	SWP-B	Ni: 30u"min
4	HOOK	1PC	SUS304	Clean
3	Housing	1PC	S475 30%G.F	UL94V-0; Color BLACK
2	Shell	1PC	SUS304	Solder plating gold flash
1	Terminal	1PC	C5210	Contact gold flash plating ;solder plating gold flash
NO	Description	Dosage	Material	Color/plating

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE MICRO SD BOT H1.80MM P/P				
X :±0.30	X :±2°	DWN	xiong	PART NO. MR-1206-P8		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY						