









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



- NOTES—
- 1.Electrical:
Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.
 - 2.Mechanical:
MATE AND UNMATE FORCE:
MATE FORCE:4.5kg MAX
UNMATE FORCE:0.5kg MIN
Durability:1500cycles MIN.
 - 3.Environment:
Operating Temperature:−25°to+85°.
 - 4.FINISH:
TERMINAL: GOLD Plated Over NICKEL
Contact area,TIN ON
SOLDER TAIL AREA& TIN
Plated ALL Over NICKEL.
Shell: SPCC WITH NICKEL&GOLD Plated.
 - 5.COLOR:
HOUSING:BLACK.



Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1

序号	DIM A	料号
1	2.65H	TF-028-H265
2	2.85H	TF-028-H285
3	3.00H	TF-028-H300
4	3.35H	TF-028-H335
5	3.75H	TF-028-H375
6	5.20H	TF-028-H520

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:		短型 TF CARD 无侦测 H=2.65-5.2H			
ANGLES:		DWN xiong PART NO. TF-028-HXXX			
X :±0.45		CHKD lee SCALE:1:1 UNIT: mm			
X.X :±0.35		APVD wang SIZE: A4 SHEET:1OF 1 REV: A4			
X.XX :±0.25		CUSTOMER COPY			