







REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:


1. MATERIAL:

INSULATOR: HIGH TEMPERATURE THERMO PLASTIC
FLAMMABILITY RATING: UL94V-0 COLOR: BLACK
CONTACT: COPPER ALLOYS
COVER: STAINLESS STEEL

2. CONTACT AREA PLATING: GOLD 15U" OVER NI
3. SOLDER TAIL COPLANARITY MUST BE WITHIN 0.10MAX.



PIN NO.	NAME
#01	DAT2
#02	CD/DAT3
#03	CMD
#04	VDD
#05	CLK
#06	VSS
#07	DAT0
#08	DAT1



RECOMMENDED PCB LAYOUT(TOP VIEW)

GENERAL TOLERANCES:±0.05

SOLDER AREA

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	T-FLASH CARD HINGED 1.9H 掀盖卡			
DWN	xiong	PART NO. TF-030		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				