



4

3

2




1



CIRCUIT DESCRIPTION

NOTES:

1. 额定值 RATING: 16A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16(6)A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16A 42VDC 40T125 (UL,CUL; ENEC17; N; CQC)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE



电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

	→		→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
	→		→	RANGE	TOLERANCE					SCALE		NO		
	→		→	X	±0.30					MAT'L		***		
	→		→	X.X	±0.20					MATERIAL NO.		DRAWING NO.		REV.
	→		→	X.XX	±0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				FR04-217B3Q16L-R		*****	A0	

4

3

2

1