






4 3 2 1



CIRCUIT DESCRIPTION

NOTES:

1. 额定值 RATING: 16A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16(6)A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16A 42VDC 40T125 (UL,CUL; ENEC17; N; CQC)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE



电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO	
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***	
2	→	7	→	X.X	±0.20					MATERIAL NO.		
1	→	6	→	X.XX	±0.10	LEGION ELECTRONIC & HARDWARE CO., LTD.				DRAWING NO.		REV.
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°					FR04-308B3Q16L-R		A0

4 3 2 1